



**OptConnect Repackaging Instructions**

**RMA**

2/5/21

## OptConnect Kit

When returning an OptConnect, please ensure that the complete kit is returned:

- 1x Router



- 1x Power Supply



- 1x Ethernet Cable



**AND**

- 1x Gemeni Antenna



**OR**

- 2x Taoglass Anten



# OptConnect Repackaging Options

## Option 1 - Off-The-Shelf Packaging

- The OptConnect can be returned in a standard corrugated box with adequate interior packaging:
  - Overbox must have dimensions  $\geq 6" \times 5" \times 2"$  and should not exceed  $12" \times 12" \times 6"$ 
    - An example of an acceptable box is [S-22612](#) from Uline
  - Kraft paper, bubble wrap, or a comparable material, must be used to fill all empty volume within the packed box
  - The box must be securely taped shut



## OptConnect Repackaging Options

### Option 2 - Within Machine Packaging (if returning machine at same time)

If returning a complete Bevi standup or countertop machine, an OptConnect may be returned within the machine packaging

#### ■ Standup

- Remove the antenna and antenna wire from the outside of the machine
- Place the router, antenna, power supply, and ethernet cord in a box, envelope, or taped within a bubble wrap enclosure
- Place the packaged kit on the CO2 shelf
- Tape the packaged kit to the shelf to reduce movement during transit

#### ■ Countertop

- Remove the antenna and antenna wire from the outside of the machine
- Place the router, antenna, power supply, and ethernet cord in padded envelope or bubble wrap enclosure
- Tape the packaged kit within the dispense area cavity (i.e. below the nozzle) along with the drip tray



# OptConnect Shipping Specification

## Shipping Specifications

A packaged OptConnect has the following dimensions:

- 6" W x 5" L x 2" H - Note that these dimensions will change based off the box that is used
- 3 lb
- Country of Origin = USA
- Ship via parcel services

**Questions?**

**Please reach out to [support@bevi.co](mailto:support@bevi.co)**

